

VELOPEX EXTRA-XE SALIENT FEATURES

This versatile machine handles all film sizes from intra-oral to panoramic and full skull, delivering processed dry to dry radiographs of consistently high diagnostic quality in just four minutes.


Automatic Processing:

The Velopex Extra-XE is very easy to use. Once switched on, the chemical is brought to working temperature automatically. It is then only necessary to press the 'RUN' button - and films can be posted through the entry slot in any order and of any size. They are developed dry-to-dry in 4 minutes without further attention. After processing, the machine switches to stand-by mode, maintaining the correct temperature for immediate further use.

Unique Film Transport System:

The key to the performance and efficiency is the unique Velopex film transport system in which x-rays are kept stationary and gently protected between two continuous permeable belts.

This well-proven system virtually eliminates the risk of film loss and ensures uniform exposure to the chemicals for consistently excellent results.



High Quality Radiographs:

Dry-to-dry radiographs of high quality in just four minutes, supporting the dentist's diagnosis while the patient is still in the surgery. The Extra-XE saves time and reduces patient recalls by making x-rays available promptly and conveniently - and there is a 'fast lane' feature to produce endodontic film for viewing wet within two minutes.

Daylight or Darkroom Operation:

The Extra-X is supplied with a capacious and convenient daylight loader - eliminating the need for a darkroom and the associated risk of film fogging. The loader can be fitted to the darkroom model at any time. Staff is no longer obliged to work with chemicals in a dark, confined space.

Deep Processing Tanks:

The deep chemical tanks provide for a long film path to allow generous film contact with the processing solutions. The slim shape of the tanks keeps the surface area small,

reducing the effects of chemical oxidation and evaporation.

Compact and Easily Installed:

Occupying little space the Extra-X is among the most compact automatic processors in its class. Installation is very simple, and requires only a suitable power socket, cold water supply and water outlet.

Minimal Maintenance:

Routine chemical replacement and cleaning are quick and straightforward. The machine is designed for a long life, maximum reliability and simple maintenance. The unique modular construction of the transport system ensures that, in the unlikely event that a film transport module requires renewal, the module can be replaced in a matter of seconds at modest cost.

Dimensions:

Width - 510mm

Depth - 740mm (with loader) - Depth - 470mm (no loader)

Height - 340mm